# DT-202C Oil-less Cabinet Low Noise Air Compressor 無油式箱型靜音空壓機









# Oil-less Pure Clean Air

無油壓縮空氣 清新純淨環保













Specs. 規格 型式	Motor (hp/kw) 馬 達	Max. Working Pressure (Kg/cm <sup>2</sup> g) 最高使用壓力	Frequency (Hz) 類 率	Speed (r.p.m) 轉速	Displacement (I/min) 活塞變位量	Noise Level dB(A) 噪音值	Tank Capacity (liter) 氣桶容量	Dimension LxWxH (mm) 尺 寸	Weight (kg) 重 ■
DT-202C	2 / 1.5	10	50	1450	230	63	30	740X620X995	150
			60	1740	236				149

<sup>\*</sup>Keep on developing for excellence, we reserve the right to alter specifications without prior notice.

本公司不斷研究改進,規格如有變更,恕不另行通知。

<sup>※</sup>Other special discharge, pressure and drive type are available upon request. 規格外之壓力、排氣量、空壓設備,詳細資料歡迎與本公司洽詢。



## **Low Noise**

低障音









### Oil-less 無油式 Low Noise 低噪音 High Reliability 高信賴

The MEDPAC dental series of compressors are specially innovated to meet the most precise standard for dental medical applications, and make them to be environmentally friendly.

MEDPAC無油式空氣壓縮機秉持綠色環 保和安全品質的理念,開發適合醫療、 食品及精密行業使用的系列機種。

#### 1 Oil-less Air Compressor Unit

- · With high quality and reliable components.
- Air tank is equipped with anti-vibration pads to achieve low Vibration while operating.
- High efficient motor with over-current Protector Switch on the Control Panel.
- · Air discharge tube is made of stainless steel.
- 無油式空壓機單元
- 高品質、高信賴度組件。
- 低震動、機體及儲氣桶. 附有緩衝墊吸震效果佳。
- 馬達效率高,盤面附有電流保護開關。
- 排氣管採用不銹鋼軟管。

#### 2 Components Of Control System

- High Reliable components: pressure switch, check valve, pressure gauge, safety valve.
- Equipped with Emergency Stop Push Button and accumulative running-hour Meter to ensure safety operation and easy to do preventive maintenance.
- 控制系統元件
- ·採用高信賴度組件:壓力開關、逆止閥、壓力錶、安全閥。
- ・附有緊急停止開關及累時計,確保操作安全性及易於執行預防保養。

#### 3 Dryer System

- With high efficient Inter-Cooler, Auto-Drain device, and Adsorptive Air Dryer to achieve dry, clean, oil-free air.
- 乾燥機系統
- 採用效能佳中間冷卻器及濾水器搭配吸附式乾燥器達到 低水份的潔淨空氣。

#### 4) Air Tank

- · Inner surface is coated with epoxy to avoid rusting (optional).
- Made of high strength steel and designed in accordance with ASME standard.
- · Equipped with safety valve to ensure safe operation.
- ●儲氣桶
- 桶內環氧樹脂塗裝,無銹蝕之慮。
- 採用高強度鋼板・依照ASME規範設計・安全可靠。
- 裝有安全閥 · 確保使用安全。

#### 5) The whole cabinet structure

- · Powder coating to create exquisite and long-lasting appearance.
- With high grade sound-absorbing material and anti-vibration structure to achieve low-noise, low-vibration while running.
- With high performance cooling Fan and deflectors to effectively cool down the components inside and ensure durable operation.
- · Equipped with Wheels for easy movement.
- 箱體結構
- · 粉體塗裝, 外觀精美耐用。
- 採用高級吸音材、防震結構、運轉低噪音、低震動。
- 冷卻系統,採用效能佳吸、排冷卻風扇,強制冷卻、 確保機體、組件壽命。
- · 底座附有活動輪,易於搬運移動。

### Absolutely Clean Air Much More Reliable And Durable

絕對清淨的空氣 高信賴度,更耐用











ISO 9001:2008



TC-2015 11-

Since 1956

www.swanair.com.tw



#### 東正鐵之款 股份有限公司 TONG CHENG IRON WORKS CO., LTD

□ : 台中市東區信義街 1 1 6 號

TEL:886-4-2261-2135 FAX:886-4-2261-5465

廠 址:台中市南區大慶街二段 1 6 號

TEL:886-4-2261-2135 FAX:886-4-2262-8246。

台北營業所:新北市五股區五權五路43號 TEL:02-2299-1285 FAX:02-2298-2296

台中營業所:台中市南區大慶街二段16號 TEL:04-2261-2135 FAX:04-2261-5465

台南營業所:台南市永康區中正南路635號 TEL:06-253-9848 FAX:06-253-9849

#### Head Office:

16 Ta Chin St. Sec.2, Taichung, Taiwan
TEL:886-4-2261-2135 FAX:886-4-2262-8246
Reg. Office:

116 Shing Yee St., Taichung, Taiwan TEL:886-4-2261-2135 FAX:886-4-2261-5465